

201 Type 1 Ni-Resist Iron

General Description:

Dura-Bar Ni-Resist irons contain an austenitic matrix of approximately 10% alloy carbides. The austenitic structure is suitable for corrosive environments in sour well oils, salts, salt water acids and alkalis. The iron is relatively soft and chrome is added to produce carbides that help improve wear resistance. Ni-Resist is denser than gray or ductile irons and has a higher coefficient of thermal expansion. Dura-Bar Type 1 Ni-Resist is manufactured to produce a material conforming to ASTM A436.

Microstructure:



The microstructure will consist of Type VII, A, size 4-6 graphite as defined in ASTM A247. The matrix will be austenite with 5-10% alloy carbide. The edge or rim will contain Type D graphite, size 6-8. Chill carbides are less than 5% in any field at 100x and will be well dispersed.

Heat Treat Response:

Austenitic alloys cannot be hardened by heat treatment. They may be softened and homogenized by heating to 1800-1900° F (980-1040° C) for three to five hours and air-cooling. This breaks down some of the carbides and most of those remaining will be spheroidized. Anneal softens the material without detrimental effect on the strength properties. Type 1 Ni-Resist should not be used in applications involving service above 1300° F (430° C).

Chemical Composition:

Element	Percentage
Carbon*	3.00% Max
Silicon*	1.00 - 2.80%
Manganese	0.50 - 1.50%
Nickel	13.50 - 17.50% Max
Copper	5.50 - 7.50%
Chromium	1.50 - 2.50%
Sulfur	0.12% Max

*Carbon and silicon targets are specified for each bar size in order to control the size and shape of the graphite flake. Titanium is added as an inoculant in order to produce the Type D graphite structure.

Mechanical Properties:

Brinell hardness values for nominal as-cast diameters are shown in the table. Hardness properties listed are minimum and maximum across the bar. Hardness values for rectangles and squares are a function of the height and width ratios and will be supplied on request. BHN in the center of bars 1.750" and smaller may be lower than the values shown because of thermal center microshrinkage.

Size Range		BHN	
Inches	mm	Min	Max
1.000 – 6.000	25 - 152	131	183

The tensile strength of 201 Type 1 Ni-Resist will be approximately 25,000 psi for bars up to 3.00" diameter and 20,000 psi for bars larger than 3.00". Tensile strength tests in bars 1.750" and smaller may not be accurate because of thermal center microshrinkage.

Mechanical Properties	
Tensile strength psi (min)	20,000
Yield strength psi (min)	N/A *
Elongation (min)	N/A*

Typical Applications:

Miscellaneous: Insecticide Pumps, Piston Ring Inserts, Sea Water Valves

Transportation: Valve Guides

Visit www.dura-bar.com/applications/index.cfm to see successful applications being made from Dura-Bar, including their design and cost benefits.

Contact us today to discuss your application and how you can start saving with Dura-Bar..